

Hyper Index 167 (MR7) Aspheric Bifocal Curve Top C28

ASAHI-LITE®

Diameter (mm)	Nominal convex curve (D)	Power range at main meridian (D)	Actual convex curve (N=1.53) (D)	Radius of curvature (mm)	Sagitta depth gauge 50mm bell (mm)	Nominal concave curve (N=1.53) (D)	Center thickness (mm)	Edge thickness (mm)	Add. powers in 0.25 D steps (D)
75	2.50	-6.00 to -1.75	1,98	267,418	1,31	7,98	5,8	14,5	1.00 to 4.50
75	4.00	-1.50 to +1.50	3,21	165,215	1,90	6,40	5,0	10,0	1.00 to 4.50
75	5.50	+1.75 to +3.75	4,36	121,434	2,50	4,78	7,0	8,0	1.00 to 4.50
70	7.00	+4.00 to +6.00	5,69	93,115	3,26	4,78	8,0	7,5	1.00 to 4.50

